

PRODUCT INFORMATION PACKET

FASCO®

Model No: D437

Catalog No: D437

Refrigeration Motor, 1 Ph, 50 Hz, 115 V, 1550/1300 RPM, 1 Speed, 3.3" Diameter, TEAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Output Watts	16 W	Frequency	50 Hz
Voltage	115 V	Current	1.30 A
Speed	1550/1300 rpm	Service Factor	1
Phase	1	Duty	Continuous Air Over
Insulation Class	B	Frame	3.3
Enclosure	Totally Enclosed Air Over	Thermal Protection	Thermally Protected
Ambient Temperature	40 °C	UL	Recognized
CSA	Y	CE	N
Number of Speeds	1		

Technical Specifications

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	4	Rotation	Counterclockwise Shaft End
Mounting	Extended Studs	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Rolled Steel
Shaft Type	Threaded	Frame Length	2.48 in
Shaft Diameter	0.312 in	Shaft Extension	1.12 in
Outline Drawing	7163480119_S001		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022