

PRODUCT INFORMATION PACKET

FASCO®

Model No: D459

Catalog No: D459

OEM Replacement Motor, 1/15 HP, 1 Ph, 60 Hz, 230/460 V, 3000 RPM, 1 Speed, 3.3" Diameter, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Phase	1	Output HP	1/15 Hp
Output KW	0.05 kW	Voltage	230/460 V
Speed	3000 rpm	Service Factor	1
Frame	3.3	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
Frequency	60 Hz	Current	1.2/6 A
Duty	Air Over	Insulation Class	B
UL	No	CSA	N
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	2	Rotation	Clockwise Shaft End
Mounting	Extended Studs	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Steel
Shaft Type	Flat	Overall Length	10.20 in
Frame Length	4.52 in	Shaft Diameter	0.250 in
Shaft Extension	3 in		
Connection Drawing	SEE OUTLINE	Outline Drawing	71219007

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:05/09/2023