

PRODUCT INFORMATION PACKET

FASCO®

Model No: D474

Catalog No: D474

Condenser Fan Motor, 1/10 HP, 1 Ph, 60 Hz, 115/208-230 V, 1550 RPM, 1 Speed, 42 Frame, OAO



Regal and FASCO are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Phase	1	Output HP	1/10 Hp
Output KW	0.07 kW	Voltage	115/208-230 V
Speed	1550 rpm	Service Factor	1
Frame	42	Enclosure	Open Air Over
Thermal Protection	Automatic	Ambient Temperature	40 °C
Frequency	60 Hz	Current	1.9/1.0 A
Duty	Continuous	Insulation Class	B
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Resilient Rings	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Rolled Steel
Shaft Type	Flat	Overall Length	8.63 in
Frame Length	4.38 in	Shaft Diameter	0.375 in
Shaft Extension	3.25 in		
Connection Drawing	SEE OUTLINE	Outline Drawing	71850057

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:05/12/2025