

PRODUCT INFORMATION PACKET

FASCO®

Model No: D495

Catalog No: D495

Refrigeration Motor, 1/20 HP, 1 Ph, 50/60 Hz, 115/208-230 V, 1050 RPM, 1 Speed, 42 Frame, OAO



Regal and FASCO are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2026 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Phase	1	Output HP	1/20 Hp
Output KW	0.04 kW	Voltage	115/208-230 V
Speed	1050 rpm	Service Factor	1.0
Frame	42	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
Frequency	50/60 Hz	Current	3.0/1.6 A
Duty	Air Over	Insulation Class	A
UL	Recognized	CSA	Y
CE	N	A2L Status	A2L Compliant
Number of Speeds	1		

Technical Specifications

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	6	Rotation	Counterclockwise Shaft End
Mounting	Resilient Rings	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Na
Shaft Type	Flat	Overall Length	7.94 in
Shaft Diameter	0.375 in	Shaft Extension	3.15 in
Connection Drawing	SEE OUTLINE	Outline Drawing	71513365

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:05/11/2026