

PRODUCT INFORMATION PACKET

FASCO®

Model No: D534

Catalog No: D534

OEM Replacement Motor, 1/35-1/110 HP, 1 Ph, 60 Hz, 115 V, 1500 RPM, 2 Speed, 3.3" Diameter, TEAO



Regal and FASCO are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2026 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Phase	1	Output HP	1/35-1/110 Hp
Output KW	0.02 kW	Voltage	115 V
Speed	1500 rpm	Service Factor	1
Frame	3.3	Enclosure	Totally Enclosed Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
Frequency	60 Hz	Current	1.50/0.50 A
Duty	Air Over	Insulation Class	B
UL	Recognized	CSA	Y
CE	N	Number of Speeds	2

Technical Specifications

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	4	Rotation	Clockwise Shaft End
Mounting	Extended Studs	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Steel
Shaft Type	Flat	Overall Length	4.13 in
Frame Length	2.32 in	Shaft Diameter	0.250 in
Shaft Extension	1 in		
Connection Drawing	SEE OUTLINE	Outline Drawing	71634335

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:03/03/2026