

PRODUCT INFORMATION PACKET

FASCO®

Model No: D5488

Catalog No: D5488

Condenser Fan Motor, 1/6-1/8 HP, 1 Ph, 60 Hz, 208-230 V, 825 RPM, 1 Speed, 48 Frame, TEAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Output HP	1/6-1/8 Hp	Output KW	0.13 kW
Frequency	60 Hz	Voltage	208-230 V
Current	1.00 A	Speed	825 rpm
Service Factor	1	Phase	1
Duty	Continuous Air Over	Insulation Class	B
Frame	48	Enclosure	Totally Enclosed Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Permanent Split Capacitor	Poles	8
Rotation	Reversible	Mounting	Extended Studs
Motor Orientation	Any	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Double Flat	Overall Length	10.81 in
Frame Length	3.57 in	Shaft Diameter	0.500 in
Shaft Extension	6.50 in	Thru-bolts Extension	1.33 in
Connection Drawing	NP24X327691	Outline Drawing	5KCP39EFBB23S

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/17/2023