

PRODUCT INFORMATION PACKET

FASCO®

Model No: D573
Catalog No: D573
25 WATT Refrigeration Motor, 1550 RPM, 230 Volts, Unit Bearing, TEAO
Unit Bearing Motors



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Output Watts	25 W	Frequency	60 Hz
Voltage	230 V	Current	0.66 A
Speed	1550 rpm	Service Factor	1
Phase	1	Duty	Continuous Air Over
Insulation Class	B	Frame	UNIT BEARING
Enclosure	Totally Enclosed Air Over	Thermal Protection	Automatic
Ambient Temperature	40 °C	UL	Recognized
CSA	Y	CE	N
Number of Speeds	1		

Technical Specifications

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	4	Rotation	Counterclockwise Lead End
Mounting	2 BOSS/OSE 3 HOLES	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Cast Iron
Shaft Type	Threaded	Frame Length	3.85 in
Shaft Diameter	1/4x20 in	Shaft Extension	0.5 in
Outline Drawing	D573		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/11/2021