

PRODUCT INFORMATION PACKET

FASCO®

Model No: D608

Catalog No: D608

Fan and Blower Motor, 1/50 HP, 1 Ph, 50 Hz, 230 V, 2500/3000 RPM, 1 Speed, 3.3" Diameter, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2024 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Phase	1	Output HP	1/50 Hp
Output KW	0.01 kW	Voltage	230 V
Speed	2500/3000 rpm	Frame	3.3
Enclosure	Open Air Over	Thermal Protection	Thermally Protected
Efficiency	22 %	Ambient Temperature	40 °C
Frequency	50 Hz	Current	.64/.53 A
Duty	Air Over	Insulation Class	B
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	2	Rotation	Clockwise Shaft End
Mounting	Extended Studs	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Steel
Shaft Type	Flat	Overall Length	5.12 in
Frame Length	3.50 in	Shaft Diameter	0.250 in
Shaft Extension	1.30 in		
Connection Drawing	NA	Outline Drawing	71213714

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/24/2024