

PRODUCT INFORMATION PACKET

FASCO®

Model No: D633

Catalog No: D633

OEM Replacement Motor, 1/50 HP, 1 Ph, 60 Hz, 120 V, 1400 RPM, 1 Speed, 3.3" Diameter, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2024 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Phase	1	Output HP	1/50 Hp
Output KW	0.01 kW	Voltage	120 V
Speed	1400 rpm	Service Factor	1
Frame	3.3	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
Frequency	60 Hz	Current	0.76 A
Duty	Air Over	Insulation Class	B
UL	Recognized	CSA	N
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	4	Rotation	Clockwise Shaft End
Mounting	Hexagonal Hubs	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Steel
Shaft Type	Flat	Overall Length	4.34 in
Frame Length	2.32 in	Shaft Diameter	0.313 in
Shaft Extension	1.38 in		
Connection Drawing	NA	Outline Drawing	71732364-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/07/2024