

# PRODUCT INFORMATION PACKET

FASCO®

Model No: D636

Catalog No: D636

OEM Replacement Motor, 1/25 HP, 1 Ph, 60 Hz, 230 V, 1500/1200 RPM, 1 Speed, 3.3" Diameter, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2024 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



**Nameplate Specifications**

Phase	1	Output HP	1/25 Hp
Output KW	0.03 kW	Voltage	230 V
Speed	1500/1200 rpm	Service Factor	1
Frame	3.3	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
Frequency	60 Hz	Current	0.90 A
Duty	Air Over	Insulation Class	B
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

**Technical Specifications**

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Extended Studs	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Steel
Shaft Type	Flat	Overall Length	10.25 in
Frame Length	2.95 in	Shaft Diameter	0.313 in
Shaft Extension	3.5 in		
Outline Drawing	71633509	Connection Drawing	NA

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/24/2024