

PRODUCT INFORMATION PACKET

FASCO®

Model No: D701

Catalog No: D701

Fan and Blower Motor, 1/2-1/3-1/4-1/5 HP, 1 Ph, 60 Hz, 115 V, 1075 RPM, 4 Speed, 48 Frame, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Output HP	1/2-1/3-1/4-1/5 Hp	Output KW	0.37 kW
Frequency	60 Hz	Voltage	115 V
Current	7.7-5.5-4.2-3.3 A	Speed	1075 rpm
Service Factor	1	Phase	1
Duty	Continuous	Insulation Class	B
Frame	48	Enclosure	Open Air Over
Thermal Protection	Automatic	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	4

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	6	Rotation	Reversible
Mounting	Extended Studs	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Rolled Steel
Shaft Type	Double Flat	Frame Length	5.39 in
Shaft Diameter	0.500 in	Shaft Extension	5.43 in
Outline Drawing	8557PVA-A11U		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022