

# PRODUCT INFORMATION PACKET

FASCO®

Model No: D725

Catalog No: D725

Fan and Blower Motor, 1/4-1/6-1/8 HP, 1 Ph, 60 Hz, 208-230 V, 1075 RPM, 3 Speed, 48 Frame, ODP



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



**Nameplate Specifications**

Output HP	1/4-1/6-1/8 Hp	Output KW	0.19 kW
Frequency	60 Hz	Voltage	208-230 V
Current	2.2-1.5-1.1 A	Speed	1075 rpm
Service Factor	1	Phase	1
Duty	Continuous	Insulation Class	B
Frame	48	Enclosure	Open Drip Proof
Thermal Protection	Automatic	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	3

**Technical Specifications**

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	6	Rotation	Reversible
Mounting	Extended Studs	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Rolled Steel
Shaft Type	Double Flat	Frame Length	4.21 in
Shaft Diameter	0.500 in	Shaft Extension	5.94 in
Outline Drawing	8857MVA-A13U		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022