

# PRODUCT INFORMATION PACKET

**FASCO**®

Model No: D728

Catalog No: D728

Fan and Blower Motor, 3/4-1/2-1/3 HP, 1 Ph, 60 Hz, 115 V, 1075 RPM, 3 Speed, 48 Frame, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

**RegalRexnord**



### Nameplate Specifications

|                    |                     |                     |               |
|--------------------|---------------------|---------------------|---------------|
| Output HP          | 3/4-1/2-1/3 Hp      | Output KW           | 0.56 kW       |
| Frequency          | 60 Hz               | Voltage             | 115 V         |
| Current            | 10.70 A             | Speed               | 1075 rpm      |
| Service Factor     | 1                   | Phase               | 1             |
| Duty               | Continuous Air Over | Insulation Class    | B             |
| Frame              | 48                  | Enclosure           | Open Air Over |
| Thermal Protection | Thermally Protected | Ambient Temperature | 40 °C         |
| UL                 | Recognized          | CSA                 | Y             |
| CE                 | N                   | Number of Speeds    | 3             |

### Technical Specifications

|                       |                           |                      |                 |
|-----------------------|---------------------------|----------------------|-----------------|
| Electrical Type       | Permanent Split Capacitor | Poles                | 6               |
| Rotation              | Reversible                | Mounting             | Resilient Rings |
| Motor Orientation     | Any                       | Drive End Bearing    | Ball            |
| Opp Drive End Bearing | Ball                      | Frame Material       | Rolled Steel    |
| Shaft Type            | Double Flat               | Overall Length       | 12.14 in        |
| Frame Length          | 4.82 in                   | Shaft Diameter       | 0.500 in        |
| Shaft Extension       | 5.75 in                   | Thru-bolts Extension | N/R in          |
| Outline Drawing       | 5KCP39PGWF89AS            | Connection Drawing   | NP24X327365     |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022