

# PRODUCT INFORMATION PACKET



Model No: D736

Catalog No: D736

Unit Heater Motor, 1/6 HP, 1 Ph, 60 Hz, 115 V, 1625 RPM, 1 Speed, 48 Frame, CLOSED AO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





**Nameplate Specifications**

Phase	1	Output HP	1/6 Hp
Output KW	0.13 kW	Voltage	115 V
Speed	1625 rpm	Service Factor	1
Frame	48	Enclosure	Totally Enclosed Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
Frequency	60 Hz	Current	2.10 A
Duty	Continuous Air Over	Insulation Class	B
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

**Technical Specifications**

Electrical Type	Permanent Split Capacitor	Poles	4
Rotation	Counterclockwise/Clockwise	Mounting	Resilient Base
Motor Orientation	Hor	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Flat	Overall Length	8.14 in
Frame Length	3.82 in	Shaft Diameter	0.500 in
Shaft Extension	2.75 in		
Connection Drawing	NP24X350357	Outline Drawing	5KCP39GGWD64S

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/10/2025