

# PRODUCT INFORMATION PACKET

FASCO®

Model No: D790

Catalog No: D790

Condenser Fan Motor, 1/2 HP, 1 Ph, 60 Hz, 208-230 V, 825 RPM, 1 Speed, 48 Frame, OPAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



**Nameplate Specifications**

Phase	1	Output HP	1/2 Hp
Output KW	0.37 kW	Voltage	208-230 V
Speed	825 rpm	Service Factor	1
Frame	48	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	60 °C
Frequency	60 Hz	Current	3.50 A
Duty	Continuous Air Over	Insulation Class	B
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

**Technical Specifications**

Electrical Type	Permanent Split Capacitor	Poles	8
Rotation	Counterclockwise/Clockwise	Mounting	Extended Studs
Motor Orientation	Any	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Double Flat	Overall Length	11.73 in
Frame Length	4.57 in	Shaft Diameter	0.500 in
Shaft Extension	6.42 in		
Connection Drawing	NP24X327691	Outline Drawing	5KCP39NFBB26S

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/10/2025