

PRODUCT INFORMATION PACKET

FASCO®

Model No: D794

Catalog No: D794

Condenser Fan Motor, 1/5 HP, 1 Ph, 60 Hz, 208-230 V, 825 RPM, 1 Speed, 48 Frame, CLOSED AO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

| | | | |
|--------------------|---------------------|---------------------|---------------------------|
| Output HP | 1/5 Hp | Output KW | 0.15 kW |
| Frequency | 60 Hz | Voltage | 208-230 V |
| Current | 1.30 A | Speed | 825 rpm |
| Service Factor | 1 | Phase | 1 |
| Duty | Continuous Air Over | Insulation Class | B |
| Frame | 48 | Enclosure | Totally Enclosed Air Over |
| Thermal Protection | Thermally Protected | Ambient Temperature | 60 °C |
| UL | Recognized | CSA | Y |
| CE | N | Number of Speeds | 1 |

Technical Specifications

| | | | |
|-----------------------|----------------------------|----------------------|----------------|
| Electrical Type | Permanent Split Capacitor | Poles | 8 |
| Rotation | Counterclockwise/Clockwise | Mounting | Extended Studs |
| Motor Orientation | Any | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Rolled Steel |
| Shaft Type | Double Flat | Overall Length | 10.56 in |
| Frame Length | 3.82 in | Shaft Diameter | 0.500 in |
| Shaft Extension | 6.00 in | Thru-bolts Extension | 1.65 in |
| Connection Drawing | NP24X327691 | Outline Drawing | 5KCP39GFAE13AS |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:03/14/2023