

# PRODUCT INFORMATION PACKET

FASCO®

Model No: D818

Catalog No: D818

OEM Replacement Motor, 1/3 HP, 1 Ph, 60 Hz, 115 V, 825 RPM, 3 Speed, 48 Frame, OPAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



**Nameplate Specifications**

Phase	1	Output HP	1/3 Hp
Output KW	0.25 KW	Voltage	115 V
Speed	825 rpm	Service Factor	1
Frame	48	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
Frequency	60 Hz	Current	6.80 A
Duty	Continuous Air Over	Insulation Class	B
UL	Recognized	CSA	Y
CE	N	Number of Speeds	3

**Technical Specifications**

Electrical Type	Permanent Split Capacitor	Poles	8
Rotation	Counterclockwise	Mounting	Resilient Rings
Motor Orientation	Any	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Rolled Steel
Shaft Type	Flat	Overall Length	10.14 in
Frame Length	6.07 in	Shaft Diameter	0.500 in
Shaft Extension	2.50 in		
Connection Drawing	NP24X327806	Outline Drawing	5KCP39NFAE52S

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/10/2025