

# PRODUCT INFORMATION PACKET

FASCO®

Model No: D829

Catalog No: D829

OEM Replacement Motor, 1/4 HP, 1 Ph, 60 Hz, 115 V, 825 RPM, 1 Speed, 48 Frame, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



**Nameplate Specifications**

Output HP	1/4 Hp	Output KW	0.19 kW
Frequency	60 Hz	Voltage	115 V
Current	5.04 A	Speed	825 rpm
Service Factor	1	Phase	1
Duty	Continuous Air Over	Insulation Class	B
Frame	48	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

**Technical Specifications**

Electrical Type	Permanent Split Capacitor	Poles	8
Rotation	Counterclockwise/Clockwise	Mounting	Resilient Base
Motor Orientation	Hor	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Flat	Overall Length	7.89 in
Frame Length	4.82 in	Shaft Diameter	0.500 in
Shaft Extension	1.50 in	Thru-bolts Extension	N/R in
Connection Drawing	NP24X350147	Outline Drawing	5KCP39EFBB37P

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022