

PRODUCT INFORMATION PACKET

FASCO®

Model No: D894
Catalog No: D894
1/6 HP OEM Replacement Motor, 1650 RPM, 277 Volts, 48 Frame, Semi Enclosed
OEM Replacement Motors



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Output HP	1/6 Hp	Output KW	0.13 kW
Frequency	60 Hz	Voltage	277 V
Current	0.8 A	Speed	1650 rpm
Service Factor	1	Phase	1
Duty	Continuous Air Over	Insulation Class	B
Frame	48	Enclosure	Semi Enclosed
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	4	Rotation	Clockwise Shaft End
Mounting	Lug	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Rolled Steel
Shaft Type	Flat	Frame Length	3.80 in
Shaft Diameter	0.500 in	Shaft Extension	2.3 in
Outline Drawing	7124082310		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/11/2021