

PRODUCT INFORMATION PACKET

FASCO®

Model No: D913

Catalog No: D913

Condenser Fan Motor, 1/4 HP, 1 Ph, 60/50 Hz, 460 V, 1075 RPM, 1 Speed, 48 Frame, OPAO



Regal and FASCO are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

| | | | |
|--------------------|---------------------|---------------------|---------------|
| Phase | 1 | Output HP | 1/4 Hp |
| Output KW | 0.19 kW | Voltage | 460 V |
| Speed | 1075 rpm | Service Factor | 1 |
| Frame | 48 | Enclosure | Open Air Over |
| Thermal Protection | Thermally Protected | Ambient Temperature | 60 °C |
| Frequency | 60/50 Hz | Current | 1.00 A |
| Duty | Continuous Air Over | Insulation Class | B |
| UL | Recognized | CSA | Y |
| CE | Y | Number of Speeds | 1 |

Technical Specifications

| | | | |
|-----------------------|----------------------------|-------------------|----------------|
| Electrical Type | Permanent Split Capacitor | Poles | 6 |
| Rotation | Counterclockwise/Clockwise | Mounting | Extended Studs |
| Motor Orientation | Any | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Rolled Steel |
| Shaft Type | Double Flat | Overall Length | 11.34 in |
| Frame Length | 3.82 in | Shaft Diameter | 0.500 in |
| Shaft Extension | 5.90 in | | |
| Connection Drawing | NP24X350357 | Outline Drawing | 5KCP39FGWD70S |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/23/2025