

PRODUCT INFORMATION PACKET

FASCO®

Model No: D960

Catalog No: D960

Condenser Fan Motor, 1/3 HP, 1 Ph, 60 Hz, 460 V, 825 RPM, 1 Speed, 48 Frame, OPAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

| | | | |
|--------------------|---------------------|---------------------|---------------|
| Phase | 1 | Output HP | 1/3 Hp |
| Output KW | 0.25 kW | Voltage | 460 V |
| Speed | 825 rpm | Service Factor | 1 |
| Frame | 48 | Enclosure | Open Air Over |
| Thermal Protection | Thermally Protected | Ambient Temperature | 60 °C |
| Frequency | 60 Hz | Current | 1.30 A |
| Duty | Continuous | Insulation Class | B |
| UL | Recognized | CSA | Y |
| CE | N | Number of Speeds | 1 |

Technical Specifications

| | | | |
|-----------------------|----------------------------|--------------------|----------------|
| Electrical Type | Permanent Split Capacitor | Poles | 8 |
| Rotation | Counterclockwise/Clockwise | Mounting | Extended Studs |
| Motor Orientation | Any | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Rolled Steel |
| Shaft Type | Double Flat | Overall Length | 11.06 in |
| Frame Length | 4.32 in | Shaft Diameter | 0.500 in |
| Shaft Extension | 6.00 in | | |
| Outline Drawing | 5KCP39LFBB33S | Connection Drawing | NP24X327691 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/10/2025