

PRODUCT INFORMATION PACKET



Model No: 160A
Catalog No: 160A

OEM Replacement Motor, 1/3 HP, 1 Ph, 60 Hz, 208-230 V, 1625 RPM, 1 Speed, 48 Frame, SEMI ENCL



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications


Phase	1	Output HP	1/3 Hp
Output KW	0.25 kW	Voltage	208-230 V
Speed	1625 rpm	Service Factor	1.0
Frame	F48Y	Enclosure	Semi Enclosed
Thermal Protection	Automatic	Ambient Temperature	60 °C
Frequency	60 Hz	Current	3.0 A
Duty	Air Over	Insulation Class	B
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Resilient Base	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	Double Flat
Overall Length	9.11 in	Frame Length	4.00 in
Shaft Diameter	0.500 in	Shaft Extension	4.00 in
Connection Drawing	614131-242	Outline Drawing	160A-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/10/2025

1



NOTES:

- 1. FOR USE WITH 614129 NAMEPLATE BLANK
- 2. — — — — — INDICATES DIMENSION LIMITS
- 3. DIE TO BE MADE FROM MASTER SUPPLIED BY REGAL REXNORD CORPORATION
- 4. DIE MUST PRODUCE A LEGIBLE IMPRESSION.

DRAWING REVISION H	REVISION BY J. RUPERT	DATE 03-16-2022	TOLERANCES UNLESS OTHERWISE SPECIFIED DEC. INCH mm ANGLE .X ±0.1 [±2.5] ±0.5° .XX ±0.02 [±0.51] .XXX ±0.005 [±0.127] .XXXX ±0.0005 [±0.0127] REMOVE BURRS & BREAK SHARP EDGES .003/.015 [.076/.381] X 45° CORNER FILLETS R.02 [.51] MACHINED SURFACES 125/INCH mm 3.2/ mm SHOWN IN [BRACKETS]	DRAWN BY: YL	REGAL™ Regal Beloit America, Inc.						
ECO NMR-0213140	APPROVED BY J. RUPERT	DATE 03-16-2022		DATE: 04-15-2011	DESCRIPTION CONNECTION DIAGRAM EXTERNAL						
ECO DESCRIPTION REVISED FOR UP ISSUED				APPROVED BY: HZ							
COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION – THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.				DATE: 04-15-2011	MATERIAL		PROCESS/FINISH				
				REFERENCE							
							THIRD ANGLE PROJECTION	SIZE A	DWG NO 4 of 4	SHEET 1	
								614131-242			