

PRODUCT INFORMATION PACKET



Model No: B180

Catalog No: B180

Pressure Washer Motor, 5.0 HP, 1 Ph, 60 Hz, 208-230 V, 3600 RPM, R56Y Frame, DP



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	1	Output HP	5.0 Hp
Output KW	3.7 kW	Voltage	208-230 V
Speed	3450 rpm	Service Factor	1.15
Frame	R56Y	Enclosure	Drip Proof
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
Frequency	60 Hz	Current	22.0 A
Duty	Continuous	Insulation Class	B
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Capacitor Start, Capacitor Run, Single Or Dual Voltage	Starting Method	Across The Line
Poles	2	Rotation	Clockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	14.56 in
Frame Length	8.75 in	Shaft Diameter	0.875 in
Shaft Extension	2.31 in		
Connection Drawing	17947801	Outline Drawing	B180-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/27/2023

