

PRODUCT INFORMATION PACKET



Model No: B222

Catalog No: B222

Aeration Fan Motor, 1.0 HP, 1 Ph, 60 Hz, 115/230 V, 3600 RPM, L56 Frame, TEAO



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	1	Output HP	1.0 Hp
Output KW	0.75 kW	Voltage	115/230 V
Speed	3450 rpm	Service Factor	1.00
Frame	L56	Enclosure	Totally Enclosed Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
Frequency	60 Hz	Current	9.2/4.6 A
Duty	Continuous	Insulation Class	B
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Permanent Split Capacitor, Single Or Dual Voltage	Starting Method	Across The Line
Poles	2	Rotation	Reversible Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	11.06 in
Frame Length	6.25 in	Shaft Diameter	0.625 in
Shaft Extension	1.94 in		
Connection Drawing	17050801.PCX	Outline Drawing	162845-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/27/2023

