

PRODUCT INFORMATION PACKET



Model No: CS89

Catalog No: CS89

Fan Coil & Air Conditioner Motor, 1/10 HP, 1 Ph, 60 Hz, 120 V, 1100, 900, 700 RPM, 3 Speed,
42 Frame, OAO



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	1/10 Hp	Output KW	0.07 kW
Frequency	60 Hz	Voltage	120 V
Current	1.6 A	Speed	1100, 900, 700 rpm
Service Factor	1	Phase	1
Duty	Continuous	Insulation Class	B
Frame	42	Enclosure	Open Air Over
Thermal Protection	Automatic	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	3

Technical Specifications

Electrical Type	Electronically Commutated Motor	Starting Method	Across The Line
Poles	6	Rotation	Clockwise Lead End
Mounting	Resilient Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Steel
Shaft Type	Flat	Frame Length	3.80 in
Shaft Diameter	0.500 in	Shaft Extension	9.3 X 1/2 X 9.3 in
Outline Drawing	CS89		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/28/2022

