

PRODUCT INFORMATION PACKET



Model No: C860
Catalog No: C860

General Purpose Motor, 3/4-1/4 HP, 1 Ph, 60 Hz, 115 V, 1800 RPM, 56 Frame, ODP



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

| | | | |
|--------------------|---------------|---------------------|-----------------|
| Phase | 1 | Output HP | 3/4-1/4 Hp |
| Output KW | 0.56 kW | Voltage | 115 V |
| Speed | 1725/1140 rpm | Service Factor | 1.25 |
| Frame | 56 | Enclosure | Open Drip Proof |
| Thermal Protection | No Protection | Ambient Temperature | 40 °C |
| Frequency | 60 Hz | Current | 7.6/5.3 A |
| Duty | Continuous | Insulation Class | B |
| UL | Recognized | CSA | Y |
| CE | N | Number of Speeds | 2 |

Technical Specifications

| | | | |
|-----------------------|--|--------------------|----------------------------|
| Electrical Type | Capacitor Start, Capacitor Run, Single Or Dual Voltage | Starting Method | Across The Line |
| Poles | 4/6 | Rotation | Clockwise/Counterclockwise |
| Mounting | Resilient Base | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Rolled Steel |
| Shaft Type | Keyed | Overall Length | 12.19 in |
| Frame Length | 6.38 in | Shaft Diameter | 0.625 in |
| Shaft Extension | 1.94 in | | |
| Outline Drawing | C860-S01 | Connection Drawing | 624000-C112 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:08/24/2023

