

PRODUCT INFORMATION PACKET

FASCO®

Model No: D0346

Catalog No: D0346

OEM Replacement Motor, 1/4 HP, 1 Ph, 60 Hz, 115 V, 1550 RPM, 2 Speed, 3.3" Diameter, OAO



Regal and FASCO are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2026 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications



Phase	1	Output HP	1/4 Hp
Output KW	0.19 kW	Voltage	115 V
Speed	1550 rpm	Service Factor	1
Frame	3.3	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
Frequency	60 Hz	Current	2.90 A
Duty	Air Over	Insulation Class	B
UL	Recognized	CSA	N
CE	N	Number of Speeds	2

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	4	Rotation	Clockwise Shaft End
Mounting	Lug	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Steel
Shaft Type	Flat	Overall Length	10.12 in
Frame Length	4.68 in	Shaft Diameter	0.375 in
Shaft Extension	5.44 in		
Connection Drawing	00469082	Outline Drawing	71903480-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/23/2026

ΠΥΛΩΚ
 ΕΙΣ ΤΟΝ ΑΝΩΤΕΡΟΝ ΚΑΤΑΦΡΟΝΤΙΣΤΗΡΙΑΝ ΗΜΕΙΣ
 ΤΟΝ ΑΝΩΤΕΡΟΝ ΚΑΤΑΦΡΟΝΤΙΣΤΗΡΙΑΝ ΗΜΕΙΣ
 ΤΟΝ ΑΝΩΤΕΡΟΝ ΚΑΤΑΦΡΟΝΤΙΣΤΗΡΙΑΝ ΗΜΕΙΣ



ΥΠΕΡΦΟΡΟΤΗΤΑ
 ΕΙΣ ΤΟΝ ΑΝΩΤΕΡΟΝ ΚΑΤΑΦΡΟΝΤΙΣΤΗΡΙΑΝ ΗΜΕΙΣ
 ΤΟΝ ΑΝΩΤΕΡΟΝ ΚΑΤΑΦΡΟΝΤΙΣΤΗΡΙΑΝ ΗΜΕΙΣ
 ΤΟΝ ΑΝΩΤΕΡΟΝ ΚΑΤΑΦΡΟΝΤΙΣΤΗΡΙΑΝ ΗΜΕΙΣ
 ΤΟΝ ΑΝΩΤΕΡΟΝ ΚΑΤΑΦΡΟΝΤΙΣΤΗΡΙΑΝ ΗΜΕΙΣ

ΟΥΡΟΦΟΡΟΤΗΤΑ ΟΥΡΟΦΟΡΟΤΗΤΑ ΟΥΡΟΦΟΡΟΤΗΤΑ ΟΥΡΟΦΟΡΟΤΗΤΑ	ΟΥΡΟΦΟΡΟΤΗΤΑ ΟΥΡΟΦΟΡΟΤΗΤΑ ΟΥΡΟΦΟΡΟΤΗΤΑ ΟΥΡΟΦΟΡΟΤΗΤΑ	ΟΥΡΟΦΟΡΟΤΗΤΑ ΟΥΡΟΦΟΡΟΤΗΤΑ ΟΥΡΟΦΟΡΟΤΗΤΑ ΟΥΡΟΦΟΡΟΤΗΤΑ	ΟΥΡΟΦΟΡΟΤΗΤΑ ΟΥΡΟΦΟΡΟΤΗΤΑ ΟΥΡΟΦΟΡΟΤΗΤΑ ΟΥΡΟΦΟΡΟΤΗΤΑ	ΟΥΡΟΦΟΡΟΤΗΤΑ ΟΥΡΟΦΟΡΟΤΗΤΑ ΟΥΡΟΦΟΡΟΤΗΤΑ ΟΥΡΟΦΟΡΟΤΗΤΑ	ΟΥΡΟΦΟΡΟΤΗΤΑ ΟΥΡΟΦΟΡΟΤΗΤΑ ΟΥΡΟΦΟΡΟΤΗΤΑ ΟΥΡΟΦΟΡΟΤΗΤΑ
--	--	--	--	--	--