

PRODUCT INFORMATION PACKET



Model No: DC123
Catalog No: DC123
SCR Motor, 3/4 HP, 90 V, 1750 RPM, SS56C Frame, TEFC



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	3/4 Hp	Output KW	0.56 kW
Voltage	90 V	Speed	1750 rpm
Service Factor	1	Frame	SS56C
Enclosure	Totally Enclosed Fan Cooled	Thermal Protection	No Protection
Ambient Temperature	40 °C	Current	7.6 A
Duty	Continuous	Insulation Class	H
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	DC Permanent Magnet	Starting Method	Across The Line
Rotation	Reversible	Mounting	Rigid Base
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	Keyed
Overall Length	13.81 in	Frame Length	9.50 in
Shaft Diameter	0.625 in	Shaft Extension	2.06 in
Outline Drawing	612-0076-DC123		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/28/2023

