

PRODUCT INFORMATION PACKET



Model No: F683
Catalog No: F683

Direct Drive Fan Motor, 1/3 HP, 1 Ph, 60 Hz, 115 V, 1800 RPM, J56Z Frame, TEAO



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	1/3 Hp	Output KW	0.25 kW
Frequency	60 Hz	Voltage	115 V
Current	4.8 A	Speed	1725 rpm
Service Factor	1	Phase	1
Duty	Continuous	Insulation Class	B
Frame	J56Z	Enclosure	Totally Enclosed Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	55 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Split Phase, Induction Run, Single Or Dual Voltage	Starting Method	Across The Line
Poles	4	Rotation	Reversible Counterclockwise
Mounting	Round	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	11.12 in
Frame Length	5.13 in	Shaft Diameter	0.498 in
Shaft Extension	2.00 in		
Connection Drawing	17050314.PCX	Outline Drawing	162915-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/28/2022

