

PRODUCT INFORMATION PACKET

Model No: F264V1

Catalog No: F264V1

Convection Oven Motor, 1/3 - .09 HP, 1 Ph, 60 Hz, 100-115 V, 1800 RPM, 56Y Frame, DP



Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

Nameplate Specifications

| | | | |
|--------------------|---------------------|---------------------|---------------|
| Output HP | 1/3 - .09 Hp | Output KW | 0.25 kW |
| Frequency | 60 Hz | Voltage | 100-115 V |
| Current | 6.2-6.0/3.0-2.8 A | Speed | 1725/1140 rpm |
| Service Factor | 1.35 | Phase | 1 |
| Duty | Continuous | Insulation Class | B |
| Frame | 56Y | Enclosure | Drip Proof |
| Thermal Protection | Thermally Protected | Ambient Temperature | 60 °C |
| UL | Recognized | CSA | Y |
| CE | N | Number of Speeds | 2-2-VT |

Technical Specifications

| | | | |
|-----------------------|-----------------------------------------|-------------------|-----------------------------|
| Electrical Type | Split Phase, Induction Run, Multi-Speed | Starting Method | Across The Line |
| Poles | 4/6 | Rotation | Reversible Counterclockwise |
| Mounting | Rigid Base | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Rolled Steel |
| Shaft Type | Keyed | Overall Length | 12.25 in |
| Frame Length | 4.75 in | Shaft Diameter | 0.625 in |
| Shaft Extension | 4 in | | |
| Connection Drawing | 18390914.PCX | Outline Drawing | 18511301 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/07/2022

