

PRODUCT INFORMATION PACKET



Model No: H492

Catalog No: H492

Pool Pump Motor, 3/4 HP, 3 Ph, 60 Hz, 208-230/460 V, 3600 RPM, Y56Y Frame, DP



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2024 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	3	Output HP	3/4 Hp
Output KW	0.56 kW	Voltage	208-230/460 V
Speed	3450 rpm	Service Factor	1.65
Frame	Y56Y	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	50 °C
Frequency	60 Hz	Current	SF 3.8-3.6/1.8 A
Duty	Continuous	Insulation Class	B
UL	Recognized	CSA	Y
Number of Speeds	1		

Technical Specifications

Electrical Type	Polyphase, Induction Type, Single Or Dual Voltage	Starting Method	Across The Line
Poles	2	Rotation	Reversible Clockwise
Mounting	Round	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	1/2 Thread
Overall Length	12.80 in	Frame Length	8.38 in
Shaft Diameter	0.625 in	Shaft Extension	0.91 in
Outline Drawing	H492-S01	Connection Drawing	18304024.PCX

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/14/2024



1

1

3 of 3