

PRODUCT INFORMATION PACKET

Model No: H539L

Catalog No: H539L

3.0 HP General Purpose Motor, 3 phase, 1800 RPM, 460/230 V, 56HZ Frame, ODP



Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

Nameplate Specifications

Output HP	3.0 Hp	Output KW	2.2 kW
Frequency	60 Hz	Voltage	460/230 V
Current	4.6/9.2 A	Speed	1725 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	B
Frame	R56HZ	Enclosure	Open Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Polyphase, Induction Type, Single Or Dual Voltage	Starting Method	Across The Line
Poles	4	Rotation	Reversible Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	14.56 in
Frame Length	8.75 in	Shaft Diameter	0.875 in
Shaft Extension	2.31 in		
Connection Drawing	17564815.PCX	Outline Drawing	H539L-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/09/2022

REV		EDD		REV BY		DATE		APPD		DATE	
B		0025407		JAGUILERA		04-16-2012		R.RASCON		04-16-2012	

