

PRODUCT INFORMATION PACKET



Model No: FEH1026SU
Catalog No: FEH1026SU

HEATMASTER® ULTRA Condenser Fan Motor, 1/4 HP, 1 Ph, 60 Hz, 460 V, 1075 RPM, 1 Speed, 48 Frame, TEAO



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2024 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	1	Output HP	1/4 Hp
Output KW	0.19 kW	Voltage	460 V
Speed	1075 rpm	Service Factor	1.0
Frame	48	Enclosure	Totally Enclosed Air Over
Thermal Protection	Automatic	Ambient Temperature	80 °C
Frequency	60 Hz	Current	1.0 A
Duty	Air Over	Insulation Class	F
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	6	Rotation	Reversible
Mounting	Extended Studs	Motor Orientation	Any
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	Double Flat
Overall Length	12.12 in	Frame Length	4.74 in
Shaft Diameter	0.500 in	Shaft Extension	6.5 in
Connection Drawing	614131-242	Outline Drawing	FEH1026SU_FA

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:12/14/2024

GENERAL INFORMATION:

SHAFT RUNOUT: .001 [.03] T.I.R. PER INCH LENGTH OF EXTENSION

BEARINGS: BALL

MOUNTING POSITION: ALL ANGLE

ELECTRICAL DATA:

OVERLOAD PROTECTOR: AUTOMATIC RESET (T.I. 7AM 304)

LINE LEADS: NO. 18 GA., .06 [1.5] THK. XLP 125°C INSUL.

REVERSING PLUGS: NO. 18 GA., .03 [.8] THK. XLP 125°C INSUL.

GROUND LEAD: NO. 18 GA., .03 [.8] THK. (GREEN) INSUL.


REF. FEH1026SF
NAMEPLATE DATA:

MODEL NO.: 5KCP39HGDD941S
CUST. P/N: FEH1026SU
HP: 1/4
ROT.: REVERSIBLE
RPM: 1075
TYPE: UF
FRAME: 48
VOLTS: 460
PH: 1
AMPS: 1.0
HZ: 60
INS.: F
AMB.: 80°C
DUTY: AIR OVER
CAP.: 7.5 MFD/370 V
THERMALLY PROTECTED




MADE IN INDIA

EXTERNAL CONNECTION
DIAGRAM



614131-242



GREEN (GROUND)	12.0/13.0 [305/330]	#10 EYELET
BLACK/WHITE	3.0/5.0 [76/127]	REVERSING PLUG
BROWN	48.0/51.0 [1219/1295]	.25 [6.4] FLAG
BROWN/WHITE	48.0/51.0 [1219/1295]	.25 [6.4] FLAG
WHITE	48.0/51.0 [1219/1295]	.50 [12.7] SKIN
BLACK	48.0/51.0 [1219/1295]	.50 [12.7] SKIN
COLOR	LENGTH	TERMINAL OR STRIP LENGTH

REGAL-BELOIT CORPORATION (RBC) PROVIDES TECHNICAL ASSISTANCE TO OUR CUSTOMERS IN SEVERAL AREAS. SINCE RBC DOES NOT RECEIVE ALL DATA CONCERNING THE USE AND APPLICATION OF THE MOTOR, THE SUITABILITY OF THE MOTOR FOR THE APPLICATION MUST BE DETERMINED BY THE CUSTOMER.

DIMENSIONS WITHOUT TOLERANCES ARE FOR REFERENCE ONLY.

MAIN FRAME - OLE	ENCLOSED
END FRAME - OLE	ENCLOSED
MAIN FRAME - LE	ENCLOSED
END FRAME - LE	ENCLOSED

- NOTES:
1. ATTACH INSTRUCTION SHEET 681572-003 ONTO SHAFT APPROX. 1.0[25] FROM WATER SLINGER (OR 69P9-3)
 2. (4)SCREWS N194P1504B9, (4) EXTRA HEX NUTS N238P15B9 & 4x SCREW 13833003 TO BE PUT IN A POLYBAG.
 3. ALL LABEL READ FROM LE
 4. SPRING SHIM IN OLE SIDE

CUSTOMER	DISTRIBUTION SERVICE
----------	----------------------

DRAWING REVISION	REVISION BY	DATE
ECO	KG	19.11.24
ECR-0238477	APPROVED BY	DATE
ECO DESCRIPTION	LS	19.11.24
CONSERVATIONIST LABEL REMOVED		


DRAWN BY:	DATE:
MK	29.05.23
APPROVED BY:	DATE:
LS	29.05.23
PROCESS/FINISH	MATERIAL
-	-
THIRD ANGLE PROJECTION	SIZE DWG NO
	C



Regal Beloit America, Inc.

MODEL-RFHP-48FR
OUTLINE

SIZE	DWG NO	SHEET
C	FEH1026SU_FA	1



NOTES:

- 1. FOR USE WITH 614129 NAMEPLATE BLANK
- 2. — — — — — INDICATES DIMENSION LIMITS
- 3. DIE TO BE MADE FROM MASTER SUPPLIED BY REGAL REXNORD CORPORATION
- 4. DIE MUST PRODUCE A LEGIBLE IMPRESSION.

DRAWING REVISION H	REVISION BY J. RUPERT	DATE 03-16-2022	TOLERANCES UNLESS OTHERWISE SPECIFIED DEC. INCH mm ANGLE .X ±0.1 [±2.5] ±0.5° .XX ±0.02 [±0.51] .XXX ±0.005 [±0.127] .XXXX ±0.0005 [±0.0127] REMOVE BURRS & BREAK SHARP EDGES .003/.015 [.076/.381] X 45° CORNER FILLETS R.02 [.51] MACHINED SURFACES 125/INCH mm 3.2/ mm SHOWN IN [BRACKETS]	DRAWN BY: YL	REGAL™ Regal Beloit America, Inc.			
ECO NMR-0213140	APPROVED BY J. RUPERT	DATE 03-16-2022		DATE: 04-15-2011	DESCRIPTION CONNECTION DIAGRAM EXTERNAL			
ECO DESCRIPTION REVISED FOR UP ISSUED				APPROVED BY: HZ				
COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION – THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.				DATE: 04-15-2011				
				REFERENCE	MATERIAL		PROCESS/FINISH	
				THIRD ANGLE PROJECTION		SIZE A	DWG NO 4 of 4	SHEET 1
				614131-242				