

PRODUCT INFORMATION PACKET



Model No: H663

Catalog No: H663

General Purpose Motor, 1.500 HP, 3 Ph, 60 Hz, 200-230/460 V, 3600 RPM, J56J Frame, DP



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	1.500 Hp	Output KW	1.1 kW
Frequency	60 Hz	Voltage	200-230/460 V
Current	4.7-4.4/2.2 A	Speed	3450/2850 rpm
Service Factor	1.3	Phase	3
Duty	Continuous	Insulation Class	B
Frame	J56J	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Polyphase, Induction Type, Single Or Dual Voltage	Starting Method	Across The Line
Poles	2	Rotation	Reversible Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Threaded	Overall Length	11.58 in
Frame Length	5.13 in	Shaft Diameter	0.625 in
Shaft Extension	2.57 in		
Outline Drawing	H663-S01	Connection Drawing	18304024.PCX

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:12/14/2022

