

PRODUCT INFORMATION PACKET



Model No: H965V1ES
Catalog No: H965V1ES
General Purpose Motor, 2.0 HP, 3 Ph, 60 Hz, 575 V, 1800 RPM, 56 Frame, DP



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2024 Regal Rexnord Corporation, All Rights Reserved. MC017097E






Nameplate Specifications

Phase	3	Output HP	2.0 Hp
Output KW	1.5 kW	Voltage	575 V
Speed	1725 rpm	Service Factor	1.2
Frame	56	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
Frequency	60 Hz	Current	2.4 A
Duty	Continuous	Insulation Class	B
UL	Recognized	CSA	N
CE	Y	Number of Speeds	1

Technical Specifications

Electrical Type	Three Phase	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	13.44 in
Frame Length	9.66 in	Shaft Diameter	0.625 in
Shaft Extension	2.23 in		
Connection Drawing	103014	Outline Drawing	108249


This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/24/2024



TO REVERSE ROTATION, INTERCHANGE ANY TWO LINE LEADS

PLATE: 41365

SLOT: 22

			TOLERANCES UNLESS SPECIFIED			DRAWN TOM 08-14-1989		
			DEC.	INCHES		CHK	ML 08-14-1989	
			.X	±.1		APPD	GK 08-14-1989	
4	ADDED REVERSAL NOTE	SVL 10-14-2013	.XX	±.02	TITLE CONNECTION DIGRAM	SCALE	1=1	
3	REDRAWN IN AUTOCAD	TAT 09-16-2004	ML .XXX	±.005		REF		
2	REDRAWN - NEW FORMAT	TOM 08-14-1989	.XXXX	±.0005	MAT'L.	FMF		
NO.	REVISION	BY & DATE	CHK	ANG	±7'30"	FINISH	PREV	
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT			RFP	CAD FILE 103014			SIZE	DRAWING NO. PAGE OF REV.
			DIST	WP		A	103014 4	