

# PRODUCT INFORMATION PACKET



Model No: ORM5488BU

Catalog No: ORM5488BU

4-in-1® Condenser Fan Motor, 1/3-1/8 HP, 1 Ph, 60 Hz, 208-230 V, 825 RPM, 1 Speed, 48 Frame,  
ENCLOSED



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





### Nameplate Specifications

|                    |            |                     |                  |
|--------------------|------------|---------------------|------------------|
| Output HP          | 1/3-1/8 Hp | Output KW           | 0.25 kW          |
| Frequency          | 60 Hz      | Voltage             | 208-230 V        |
| Current            | 1.8 A      | Speed               | 825 rpm          |
| Service Factor     | 1          | Phase               | 1                |
| Duty               | Air Over   | Insulation Class    | F                |
| Frame              | 48         | Enclosure           | Totally Enclosed |
| Thermal Protection | Automatic  | Ambient Temperature | 80 °C            |
| UL                 | Recognized | CSA                 | Y                |
| CE                 | N          | Number of Speeds    | 1                |

### Technical Specifications

|                   |                           |                       |                 |
|-------------------|---------------------------|-----------------------|-----------------|
| Electrical Type   | Permanent Split Capacitor | Starting Method       | Across The Line |
| Poles             | 8                         | Rotation              | Reversible      |
| Mounting          | Extended Studs            | Motor Orientation     | Any             |
| Drive End Bearing | Ball                      | Opp Drive End Bearing | Ball            |
| Frame Material    | Rolled Steel              | Shaft Type            | Double Flat     |
| Overall Length    | 12.25 in                  | Frame Length          | 4.25 in         |
| Shaft Diameter    | 0.500 in                  | Shaft Extension       | 6.5 in          |
| Outline Drawing   | ORM5488BU-S01             | Connection Drawing    | 614131-242      |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/16/2023

## GENERAL INFORMATION:

SHAFT RUNOUT: .001 [.03] T.I.R. PER INCH LENGTH OF EXTENSION

BEARINGS: BALL

MOUNTING POSITION: ALL ANGLE


## ELECTRICAL DATA:

OVERLOAD PROTECTOR: AUTOMATIC RESET (T.I. 7AM 304)

LINE LEADS: NO. 18 GA., .06 [.5] THK. XLP 125°C INSUL.

REVERSING LEADS: NO. 18 GA., .03 [.8] THK. XLP 125°C INSUL.

GROUND LEAD: NO. 18 GA., .03 [.8] THK. (GREEN) INSUL.



|                |                       |                          |
|----------------|-----------------------|--------------------------|
| GREEN (GROUND) | 12.0/13.0 [305/330]   | #10 EYELET               |
| BLACK/WHITE    | 3.0/5.0 [76/127]      | REVERSING PLUG           |
| BROWN          | 48.0/51.0 [1219/1295] | .25 [6.35] FLAG          |
| BROWN/WHITE    | 48.0/51.0 [1219/1295] | .25 [6.35] FLAG          |
| WHITE          | 48.0/51.0 [1219/1295] | .50 [12.7] SKIN          |
| BLACK          | 48.0/51.0 [1219/1295] | .50 [12.7] SKIN          |
| COLOR          | LENGTH                | TERMINAL OR STRIP LENGTH |

REGAL-BELOIT CORPORATION (RBC) PROVIDES TECHNICAL ASSISTANCE TO OUR CUSTOMERS IN SEVERAL AREAS. SINCE RBC DOES NOT RECEIVE ALL DATA CONCERNING THE USE AND APPLICATION OF THE MOTOR, THE SUITABILITY OF THE MOTOR FOR THE APPLICATION MUST BE DETERMINED BY THE CUSTOMER.

DIMENSIONS WITHOUT TOLERANCES ARE FOR REFERENCE ONLY.

|                  |          |
|------------------|----------|
| MAIN FRAME - OLE | ENCLOSED |
| END FRAME - OLE  | ENCLOSED |
| MAIN FRAME - LE  | ENCLOSED |
| END FRAME - LE   | ENCLOSED |

## NOTES:

1. ATTACH INSTRUCTION SHEET 69P9-3 ONTO SHAFT APPROX. 1.0[25] FROM WATER SLINGER

2. 4X SCREWS 615982-001 & 4X HEX NUTS 7555A19H01 & 4X SCREWS 13833003 TO BE PUT IN A POLYBAG.

| NAMEPLATE DATA:                                                                                                                                                                                                                                                                                            | EXTERNAL CONNECTION DIAGRAM                                                                                                                |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|
| MODEL NO.: F48AF32A01<br>CUST. P/N: ORM5488BU<br>HP: 1/3-1/8<br>ROT.: REVERSIBLE<br>RPM: 825<br>TYPE: UF<br>FRAME: 48Y<br>VOLTS: 208-230<br>PH: 1<br>AMPS: 1.8<br>HZ: 60<br>INS.: F<br>AMB.: 80°C<br>DUTY: AIR OVER<br>CAP.: 7.5 MFD/370 V<br>ENCL: ENCLOSED<br>UL LOGO<br>CSA LOGO<br>THERMALLY PROTECTED | SEP. CAP.<br>BROWN<br>BRN/WHT<br>WHITE<br>BLACK<br>LINE<br>ROTATION<br>BLACK<br>WHITE<br>CCWLE<br>WHITE<br>BLACK<br>CWLE<br>WHITE<br>BLACK |

614131-242

| PERFORMANCE CURVE NO. | TORQUE @ 825 RPM (25°C) | APPROVED SAMPLE | UL COMPONENT        | CSA                            |
|-----------------------|-------------------------|-----------------|---------------------|--------------------------------|
| C32518                | 37.2 OZ. FT.            | 0500468A        | FILE # E46412 PRGY2 | FILE # LR43341 CLASS # 4211-01 |

|                  |             |            |
|------------------|-------------|------------|
| DRAWING REVISION | REVISION BY | DATE       |
| D                | GEUNE ZHAO  | 05-23-2019 |
| ECO              | APPROVED BY | DATE       |
| ECO-0166568      | KEYUN.GONG  | 05-23-2019 |
| ECO DESCRIPTION  |             |            |
| SEE ECO          |             |            |

PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL-BELOIT CORPORATION, INC. AND IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM, WITHOUT THE WRITTEN PERMISSION OF REGAL-BELOIT CORPORATION, INC. ANY UNAUTHORIZED REPRODUCTION OR USE OF THIS DOCUMENT IS STRICTLY PROHIBITED. REGAL-BELOIT CORPORATION, INC. SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING CONSEQUENTIAL DAMAGES, ARISING FROM THE USE OF THIS DOCUMENT.

|                        |            |
|------------------------|------------|
| DRAWN BY:              | H.ZHANG    |
| DATE:                  | 01-29-2013 |
| APPROVED BY:           | C.ZHOU     |
| DATE:                  | 01-29-2013 |
| PROCESS/FINISH         |            |
| THIRD ANGLE PROJECTION |            |



Regal Beloit America, Inc.

DESCRIPTION


MODEL-RFHP-48FR  
OUTLINE

MATERIAL

SIZE DWG NO

ORM5488BU

SHEET 1



NOTES:

- 1. FOR USE WITH 614129 NAMEPLATE BLANK
- 2. — — — — — INDICATES DIMENSION LIMITS
- 3. DIE TO BE MADE FROM MASTER SUPPLIED BY REGAL REXNORD CORPORATION
- 4. DIE MUST PRODUCE A LEGIBLE IMPRESSION.

|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |                          |                    |                                                                                                                                                                                                                                                                                                                          |                                                                                                              |                                                                   |  |                |        |       |  |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------|--------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------|--|----------------|--------|-------|--|
| DRAWING REVISION<br>H                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               | REVISION BY<br>J. RUPERT | DATE<br>03-16-2022 | TOLERANCES UNLESS OTHERWISE SPECIFIED<br>DEC. INCH mm ANGLE<br>.X ±0.1 [±2.5] ±0.5°<br>.XX ±0.02 [±0.51]<br>.XXX ±0.005 [±0.127]<br>.XXXX ±0.0005 [±0.0127]<br>REMOVE BURRS & BREAK SHARP EDGES .003/.015 [.076/.381] X 45°<br>CORNER FILLETS R.02 [.51]<br>MACHINED SURFACES 125/INCH mm 3.2/<br>mm SHOWN IN [BRACKETS] | DRAWN BY:<br>YL                                                                                              | <div><div>REGAL™</div><div>Regal Beloit America, Inc.</div></div> |  |                |        |       |  |
| ECO<br>NMR-0213140                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  | APPROVED BY<br>J. RUPERT | DATE<br>03-16-2022 |                                                                                                                                                                                                                                                                                                                          | DATE:<br>04-15-2011                                                                                          | DESCRIPTION<br><div>CONNECTION DIAGRAM</div> <div>EXTERNAL</div>  |  |                |        |       |  |
| ECO DESCRIPTION<br>REVISED FOR UP ISSUED                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |                          |                    |                                                                                                                                                                                                                                                                                                                          | APPROVED BY:<br>HZ                                                                                           |                                                                   |  |                |        |       |  |
| COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED.<br>PROPRIETARY AND CONFIDENTIAL INFORMATION – THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS. |                          |                    |                                                                                                                                                                                                                                                                                                                          | DATE:<br>04-15-2011                                                                                          | MATERIAL                                                          |  | PROCESS/FINISH |        |       |  |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |                          |                    |                                                                                                                                                                                                                                                                                                                          | REFERENCE                                                                                                    |                                                                   |  |                |        |       |  |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |                          |                    |                                                                                                                                                                                                                                                                                                                          | THIRD ANGLE PROJECTION  |                                                                   |  | SIZE           | DWG NO | SHEET |  |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |                          |                    |                                                                                                                                                                                                                                                                                                                          |                                                                                                              |                                                                   |  | A              | 4 of 4 |       |  |