

# PRODUCT INFORMATION PACKET



Model No: XEL2014  
Catalog No: XEL2014

Definite Purpose Motor, 1/6 HP, 1 Ph, 60 Hz, 115 V, 1800 RPM, 48N Frame, ENCLOSED



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





### Nameplate Specifications

Phase	1	Output HP	1/6 Hp
Output KW	0.13 kW	Voltage	115 V
Speed	1725 rpm	Service Factor	1.0
Frame	48N	Enclosure	Totally Enclosed
Thermal Protection	Manual	Ambient Temperature	40 °C
Frequency	60 Hz	Current	3.2 A
Duty	Continuous	Insulation Class	B
UL	No	CSA	N
CE	N	Number of Speeds	1

### Technical Specifications

Electrical Type	Split Phase	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	N	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Rolled Steel
Shaft Type	Flat	Overall Length	7.66 in
Frame Length	3.69 in	Shaft Diameter	0.500 in
Shaft Extension	1.82 in		
Outline Drawing	11914-007	Connection Drawing	631497-001A

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/27/2023

