

PRODUCT INFORMATION PACKET

FASCO®

Model No: D1029

Catalog No: D1029

OEM Replacement Motor, 1/8 HP, 1 Ph, 60/50 Hz, 208-230 V, 1350/1620 RPM, 1 Speed, 42 Frame, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Output HP	1/8 Hp	Output KW	0.10 kW
Frequency	50 Hz	Voltage	208-230 V
Current	0.8 A	Speed	1350/1620 rpm
Service Factor	1	Phase	1
Duty	Continuous	Insulation Class	B
Frame	42	Enclosure	Open Air Over
Thermal Protection	Automatic	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	4	Rotation	Counterclockwise Shaft End
Mounting	Round Belly Band	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Rolled Steel
Shaft Type	Flat	Overall Length	5.83 in
Frame Length	3.13 in	Shaft Diameter	0.500 in
Shaft Extension	2.26 in		
Outline Drawing	7185036400_S001	Connection Drawing	SEE OUTLINE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022