

# PRODUCT INFORMATION PACKET

FASCO®

Model No: D1107

Catalog No: D1107

OEM Replacement Motor, 1/10 HP, 1 Ph, 60 Hz, 115 V, 1550 RPM, 1 Speed, 3.3" Diameter, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



**Nameplate Specifications**

|                     |               |                    |                     |
|---------------------|---------------|--------------------|---------------------|
| Output HP           | 1/10 Hp       | Output KW          | 0.07 kW             |
| Frequency           | 60 Hz         | Voltage            | 115 V               |
| Current             | 3.20 A        | Speed              | 1550 rpm            |
| Phase               | 1             | Duty               | Air Over            |
| Insulation Class    | B             | Frame              | 3.3                 |
| Enclosure           | Open Air Over | Thermal Protection | Thermally Protected |
| Ambient Temperature | 40 °C         | UL                 | Recognized          |
| CSA                 | Y             | CE                 | N                   |
| Number of Speeds    | 1             |                    |                     |

**Technical Specifications**

|                       |                  |                   |                            |
|-----------------------|------------------|-------------------|----------------------------|
| Electrical Type       | Shaded Pole      | Starting Method   | Across The Line            |
| Poles                 | 4                | Rotation          | Counterclockwise Shaft End |
| Mounting              | Round Belly Band | Drive End Bearing | Ball                       |
| Opp Drive End Bearing | Ball             | Frame Material    | Steel                      |
| Shaft Type            | Flat             | Overall Length    | 5.42 in                    |
| Frame Length          | 3.70 in          | Shaft Diameter    | 0.312 in                   |
| Shaft Extension       | 1.45 in          |                   |                            |
| Connection Drawing    | NA               | Outline Drawing   | 71638189                   |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022