

PRODUCT INFORMATION PACKET

FASCO®

Model No: D219

Catalog No: D219

Fan and Blower Motor, 1/8 HP, 1 Ph, 60 Hz, 115 V, 3000 RPM, 1 Speed, 3.3" Diameter,
TOTALLY ENCLOSED AIR



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Phase	1	Output HP	1/8 Hp
Output KW	0.10 kW	Voltage	115 V
Speed	3000 rpm	Service Factor	1
Frame	3.3	Enclosure	Totally Enclosed Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
Frequency	60 Hz	Current	1.8 A
Duty	Continuous Air Over	Insulation Class	B
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Mounting	Extended Studs	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Steel
Shaft Type	Flat	Overall Length	7.24 in
Frame Length	4.94 in	Shaft Diameter	0.312 in
Shaft Extension	2.3 in		
Connection Drawing	00469130	Outline Drawing	71622886

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/10/2025