

# PRODUCT INFORMATION PACKET

FASCO®

Model No: D337

Catalog No: D337

Fan Coil & Air Conditioner Motor, 1/8-1/10-1/12-1/15 HP, 1 Ph, 60 Hz, 115 V, 1550 RPM, 4 Speed,  
4.4" Diameter, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



**Nameplate Specifications**

Output HP	1/8-1/10-1/12-1/15 Hp	Output KW	0.10 kW
Frequency	60 Hz	Voltage	115 V
Current	4.1-2.7-2.3-1.9 A	Speed	1550 rpm
Phase	1	Duty	Air Over
Insulation Class	A	Frame	4.4
Enclosure	Open Air Over	Thermal Protection	Thermally Protected
Ambient Temperature	40 °C	UL	Recognized
CSA	Y	CE	N
Number of Speeds	4		

**Technical Specifications**

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Resilient Rings	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Na
Shaft Type	Flat	Overall Length	18.63 in
Shaft Diameter	0.500 in	Shaft Extension	7.5 in
Outline Drawing	71085191	Connection Drawing	SEE OUTLINE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022