

PRODUCT INFORMATION PACKET

FASCO®

Model No: D339

Catalog No: D339

Fan Coil & Air Conditioner Motor, 1/8-1/12 HP, 1 Ph, 60 Hz, 230 V, 1550 RPM, 2 Speed,
4.4" Diameter, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Phase	1	Output HP	1/8-1/12 Hp
Output KW	0.10 kW	Voltage	230 V
Speed	1550 rpm	Service Factor	1
Frame	4.4	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
Frequency	60 Hz	Current	2.0-1.4 A
Duty	Air Over	Insulation Class	A
UL	Recognized	CSA	Y
CE	N	Number of Speeds	2

Technical Specifications

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Resilient Rings	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Na
Shaft Type	Flat	Overall Length	17.02 in
Shaft Diameter	0.500 in	Shaft Extension	6.50 in
Outline Drawing	71085152	Connection Drawing	SEE OUTLINE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:05/23/2023