

# PRODUCT INFORMATION PACKET

FASCO®

Model No: D365

Catalog No: D365

Fan and Blower Motor, 1/25 HP, 1 Ph, 60 Hz, 115 V, 1550/1300 RPM, 1 Speed, 3.3" Diameter, OAO



Regal and FASCO are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2026 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



### Nameplate Specifications

Phase	1	Output HP	1/25 Hp
Output KW	0.03 kW	Voltage	115 V
Speed	1550/1300 rpm	Frame	3.3
Enclosure	Open Air Over	Thermal Protection	Thermally Protected
Ambient Temperature	40 °C	Frequency	60 Hz
Current	2.00 A	Duty	Air Over
Insulation Class	B	UL	Recognized
CSA	Y	CE	N
Number of Speeds	1		

### Technical Specifications

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Extended Studs	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Steel
Shaft Type	Flat	Overall Length	6.80 in
Frame Length	2.70 in	Shaft Diameter	0.313 in
Shaft Extension	1.875 in		
Connection Drawing	NA	Outline Drawing	71635756

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:03/27/2026