

PRODUCT INFORMATION PACKET

FASCO®

Model No: D515

Catalog No: D515

Fan and Blower Motor, 1/30 HP, 1 Ph, 60 Hz, 115 V, 1550 RPM, 1 Speed, 3.3" Diameter, OAO



Regal and FASCO are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2026 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

| | | | |
|--------------------|----------------------------|---------------------|----------------------|
| Phase | 1 | Output HP | 1/30 Hp |
| Output KW | 0.02 kW | Voltage | 115 V |
| Speed | 1550 rpm | Service Factor | 1 |
| Frame | 3.3 | Enclosure | Open Air Over |
| Thermal Protection | Thermally Protected | Ambient Temperature | 40 °C |
| Frequency | 60 Hz | Current | 1.30 A |
| Duty | Air Over | Insulation Class | B |
| UL | Recognized | CSA | Y |
| CE | N | Number of Speeds | 1 |

Technical Specifications

| | | | |
|-----------------------|-----------------------|-------------------|-----------------------------------|
| Electrical Type | Shaded Pole | Starting Method | Across The Line |
| Poles | 4 | Rotation | Counterclockwise Shaft End |
| Mounting | Extended Studs | Drive End Bearing | Sleeve |
| Opp Drive End Bearing | Sleeve | Frame Material | Steel |
| Shaft Type | Flat | Overall Length | 5.43 in |
| Frame Length | 2.57 in | Shaft Diameter | 0.313 in |
| Shaft Extension | 2.30 in | | |
| Connection Drawing | NA | Outline Drawing | 71638065 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/03/2026